



CLEARANCE FOR  
CONE REMOVAL



⚠ MANUAL OVER-RIDE HANDLE PROVIDED  
ONLY ON ACTUATOR ER-4-10-4 (DN TOP).

SIZE	ACTUATOR	DIMENSIONS (INCHES)							WT.(LBS)
		A	B	C	D	E	F	G	
1/4"	ER-1-2-4	2.63	5.70	5.69	4.60	0.67	1.31	2.5	6
3/8"	ER-1-2-4	2.63	5.70	5.69	4.60	0.67	1.31	2.5	6
1/2"	ER-1-2-4	2.67	5.70	5.69	4.60	0.67	1.43	2.5	6
3/4"	ER-1-2-4	3.18	5.70	5.69	4.60	0.80	1.59	2.5	7
1"	ER-2-4-4	3.74	7.01	6.99	4.25	0.94	1.87	2.5	10
1 1/4"	ER-3-4-4	4.38	7.23	6.98	4.25	1.18	2.20	3.0	12
1 1/2"	ER-3-4-4	4.86	7.72	6.98	4.25	1.43	2.49	3.0	16
2"	ER-4-10-4	5.70	11.79	7.00	7.60	1.69	2.90	4.0	31

MAX. DIFF. PRESSURE ACROSS VALVE  
SEAT MATERIAL: RP11FE  
DIMENSIONS GIVEN FOR NEMA 4 ENCLOSURE

CUSTOMER ORDER # \_\_\_\_\_  
 CUSTOMER \_\_\_\_\_  
 TAG No. \_\_\_\_\_  
 SIZE & MODEL # 1/4"-2" STD. PORT 3T-3B/  
 3/4" WATER ELECTRIC ACTUATOR  
 CERTIFIED \_\_\_\_\_ DATE \_\_\_\_\_



DL BY DW BMM  
 CHECKY  
**MD03104**